TRANSFER TAPES

Name	Tackiness	Opacity	Liner	Compatible with:	Size Available
Transfer & Seal Tape Paper Based with Rubber Adhesive	Medium	Opaque	No Liner	ColorPrint Solvents	Width: 12", 16", 24" Length: 60'
TM-850 PET w/Acrylic Adhesive	Strong	Transparent	Has Liner	Ultimate Print Nylon	Width: 20", 30", 60" Length: 30' and 90'
TM-853 PET w/Acrylic Adhesive	Light Medium	Transparent	Has Liner	ColorPrint Solvents	Width: 20" and 30" Length: 30'
TM-854 PET w/Acrylic Adhesive	Medium	Transparent	Has Liner	ColorPrint Solvents, Reflective Printables, Printable Blockout	Width: 20" and 30" Length: 30'
DTM-855 PET w/Acrylic Adhesive	Very Light	Transparent	No Liner	ColorPrint Solvents (CPS-2160, CPLV-2700 & CPS-2165 only if they have a paper liner)	Width: 12", 16", 25", and 50" Length: 60'
KTM-500/1000 PET w/Acrylic Adhesive	Strong	Transparent	Has Liner	Ultimate Print Matte, Gloss, & Turbo, Rhinestones, Subblocker Printable, Reflective Printables, and ColorPrint Solvents CPS-2160, CPLV-2700 & CPS-2165 (only if they have a clear liner)	Width: 18.75" Length: 30', 75', and 162' KTM-1000: 37.75" x 162'
HFIX-SIL PET w/Silicone Adhesive	Very Strong	Transparent	Has Liner	Large rhinestones or rhinestuds and Solvent Flock PPF-5905	Width: 19" and 38" Length: (19") 30', 75', 90', & 162' (38") 30', 75', & 162'
HFIX-LOW PET w/Acrylic Adhesive	Light	Transparent	Has Liner	Ultimate Print Nylon	Width: 19" and 38" Length: 30', 75', and 162'
HFIX-FLCK PET w/Acrylic Adhesive	Very Strong	Transparent	Has Liner	EcoPrint, GlitterFlex Printable, Glitter Twill, CPS Silver Glitter, Solvent Flock PPF-5905	Width: 19" and 38" Length: (19") 15', 30', 75', 90', & 162' (38") 30', 75', and 162'

^{*}PET resists high temperatures. PET masks are not recommended for use with the sublimation process, because PET sublimates.

Thickness

DTM-855, TM-850, TM-854, TM-853: 4 mils/100 microns

THERMO TAPE

Sizing Available: .35" x 215'

A silicone based tape used to position multi-piece designs, such as names, numbers and more, before heat pressing. After pressing, the tape is removed without leaving any sticky residue.



SpecialtyMaterials.com | 877.437.8556



Test on dazzle cloth and other moisture-wicking polyesters. Moisture-wicking materials have better adhesion when washed and dried using no fabric softener or blotted with rubbing alcohol before pressing. Be advised that dye migration has occurred with low energy dyes in polyester and poly-blend fabrics. All technical information and recommendations are based on tests we believe to be reliable. However, we cannot guarantee performance for conditions not under manufacturer's control. Before using, please determine the suitability of product for its intended use. The user assumes all risk and liability, whatsoever, in connection with the use of this product. Seller's and manufacturer's only obligation shall be to replace such quantity of the product proved to be defective by manufacturer.

^{*}Printable materials that do not require a transfer mask: Aquaprint Clear & Opaque, Clear Matte and Clear Gloss, Color Jet III Light & Dark, CL Light, CL Trim Free, and CL Dark Premium